

## T5838 Flex EVB User Guide

#### **GENERAL DESCRIPTION**

The T5838 is a digital PDM MEMS microphone. This user guide provides information on how to use the flexible evaluation board for this part, EV T5838-FX2.

This is a simple evaluation board that allows quick evaluation of the performance of PDM MEMS microphones. The small size and low profile of the flexible PCB enables direct placement of the microphone into a prototype or an existing design for an in situ evaluation. The evaluation board consists of a bottom port microphone soldered to a flexible PCB with an edge connector. Other components on the board are a 0.1 µF supply bypass capacitor and a 50  $\Omega$  series resistor on the data line. The flex edge is an 8 position 0.5mm pitch connector which mates to a standard connector such as Kyocera (MPN 046288008000846+, Digikey PN 478-5454-1-ND) or Molex (MPN 0527450897, Digikey PN WM3772TR-ND).

**Table 1** describes the functions of the wire connections. **Table 2** describes the performance specifications of the microphone flex board.

#### **TABLE 1. PIN FUNCTION DESCRIPTIONS**

Pin #	Pin label	Microphone Pin	Description
1	Т	THSEL	Threshold select input for AAD
2	G	GND	Ground
3	V	VDD	Power Supply. 1.65 - 1.98 VDC
4	D	DATA	Data output
5	С	CLK	Clock input
6	S	L/R SELECT	L/R select; Right = 0, Left = 1
7	G	GND	Ground
8	W	WAKE	Wake output for AAD




Figure 1. EV\_T5838-FX2 Schematic

# **TABLE 2. MICROPHONE PERFORMANCE SPECIFICATIONS**

Sensitivity	Typical Supply Current	SNR	АОР	Clock Frequency
High Quality Mode: -41 dBFS +/- 1	310 μΑ	68 dB	133 dBSPL	2.0 - 3.7 MHz
Low Power Mode: -26 dBFS +/- 1	120 μΑ	65 dB	119 dBSPL	400 – 800 kHz
<u>Ultrasonic Mode</u> : -41 dBFS +/- 1	500 μΑ	68 dB	133 dBSPL	4.2 – 4.8 MHz

### **EVALUATION BOARD CIRCUIT**

Figure 1 shows the schematic of the evaluation board

Figure 2 shows the flex board and layout. See the respective microphone data sheets for complete descriptions and specifications of the microphones

Figure 3 shows the dimensions of the flex board and identifies the location of the sound port.

Figure 4 shows the lid marking to verify the microphone PN






Figure 2. EV T5838-FX2 Top View




Figure 3. EV\_T5838-FX2 Dimensions in Millimeters



# T5838 Flex EVB User Guide






Figure 4. T5838 lid marking

#### **REVISION HISTORY**

REVISION DATE	REVISION	DESCRIPTION
4/19/2021	1.0	Initial release
4/5/2022	1.1	Updated Table 2 and Figure 2
8/2/2022	1.2	Updated information on flex edge connector

### **COMPLIANCE DECLARATION DISCLAIMER**

TDK believes the environmental and other compliance information given in this document to be correct but cannot guarantee accuracy or completeness. Conformity documents substantiating the specifications and component characteristics are on file. TDK subcontracts manufacturing, and the information contained herein is based on data received from vendors and suppliers, which has not been validated by TDK.

This information furnished by TDK, Inc. ("TDK") is believed to be accurate and reliable. However, no responsibility is assumed by TDK for its use, or for any infringements of patents or other rights of third parties that may result from its use. Specifications are subject to change without notice. TDK reserves the right to make changes to this product, including its circuits and software, in order to improve its design and/or performance, without prior notice. TDK makes no warranties, neither expressed nor implied, regarding the information and specifications contained in this document. TDK assumes no responsibility for any claims or damages arising from information contained in this document, or from the use of products and services detailed therein. This includes, but is not limited to, claims or damages based on the infringement of patents, copyrights, mask work and/or other intellectual property rights.

Certain intellectual property owned by TDK and described in this document is patent protected. No license is granted by implication or otherwise under any patent or patent rights of TDK. This publication supersedes and replaces all information previously supplied. Trademarks that are registered trademarks are the property of their respective companies. TDK sensors should not be used or sold in the development, storage, production or utilization of any conventional or mass-destructive weapons or for any other weapons or life threatening applications, as well as in any other life critical applications such as medical equipment, transportation, aerospace and nuclear instruments, undersea equipment, power plant equipment, disaster prevention and crime prevention equipment.

©2022 TDK. All rights reserved. TDK, MotionTracking, MotionProcessing, MotionProcessor, MotionFusion, MotionApps, DMP, AAR, and the TDK logo are trademarks of TDK, Inc. The TDK logo is a trademark of TDK Corporation. Other company and product names may be trademarks of the respective companies with which they are associated.

