Document Number: DS-000081

Revision: 1.0

Release Date: 06/15/2015



ICM-20608-G Datasheet Revision 1.0



TABLE OF CONTENTS

TAE	BLE OF CO	DNTENTS	2
Tab	le Of FIG	URES	4
Tab	le Of TAE	BLES	4
1.	Gene	ral Description	5
	1.2	Purpose and Scope	5
	1.3	Product Overview	5
	1.4	Applications	5
2.	Featu	ires	6
	2.1	Gyroscope Features	6
	2.2	Accelerometer Features	6
	2.3	Additional features	6
3.	Electr	rical Characteristics	7
	3.1	Gyroscope Specifications	7
	3.2	Accelerometer Specifications	8
	3.3	Electrical Specifications	9
	3.3.1	D.C. Electrical Characteristics	9
	3.3.2	Standard (Duty-Cycle) Mode Noise and Power Performance:	10
	3.3.3	A.C. Electrical Characteristics	11
	3.3.4	Other Electrical Specifications	13
	3.4	I2C Timing characterization	14
	3.5	spi Timing characterization	15
	3.6	Absolute Maximum Ratings	16
4.	Appli	cations Information	17
	4.1	Pin Out Diagram and Signal Description	17
	4.2	Typical Operating Circuit	18
	4.3.	bill of materials for external components	19
	4.4.	Block Diagram	19
	4.5.	Overview	20
	4.6.	Three-Axis MEMS Gyroscope with 16-bit ADCs and Signal Conditioning	20
	4.7.	Three-Axis MEMS Accelerometer with 16-bit ADCs and Signal Conditioning	20
	4.8.	I2C and SPI Serial Communications Interfaces	20
	4.8.1	ICM-20608-G Solution Using I2C Interface	20
	4.8.2	ICM-20608-G Solution Using SPI Interface	21
	4.9	Self-Test	22
	4.10	Clocking	22
	4.11	Sensor Data Registers	22
	4.12	FIFO	22
	4.13	Interrupts	22



	4.14	Digital-Output Temperature Sensor	22
	4.15	Bias and LDOs	23
	4.16	Charge Pump	23
	4.17	Power Modes	23
5	Progr	ammable Interrupts	24
	5.1	Wake-on-Motion Interrupt	24
6	Digita	ıl Interface	25
	6.1	I2C and SPI Serial Interfaces	25
	6.2	I2C Interface	25
	6.3	I2C Communications Protocol	25
	6.4	I ² C Terms	27
	6.5	SPI Interface	28
7	Asser	nbly	29
	Orien	tation of Axes	29
	Packa	ge Dimensions	30
8	Part I	Number Package Marking	32
9.Ref	erence		33
	Revis	ion History	34
	Comp	oliance Declaration Disclaimer	35



TABLE OF FIGURES

Figure 1. I2C Bus Timing Diagram	14
Figure 2. SPI Bus Timing Diagram	15
Figure 3. Pin out Diagram for ICM-20608-G 3.0x3.0x0.75mm LGA	17
Figure 4. ICM-20608-G I2C Operation Application Schematic	18
Figure 5. ICM-20608-G SPI Operation Application Schematic	18
Figure 6. ICM-20608-G Block Diagram	19
Figure 7. ICM-20608-G Solution Using I ² C Interface	21
Figure 8. ICM-20608-G Solution Using SPI Interface	21
Figure 9. START and STOP Conditions	25
Figure 10. Acknowledge on the I ² C Bus	26
Figure 11. Complete I ² C Data Transfer	26
Figure 12. Typical SPI Master/Slave Configuration	28
Figure 13. Orientation of Axes of Sensitivity and Polarity of Rotation	29
TABLE OF TABLES Table 1. Gyroscope Specifications	7
Table 2. Accelerometer Specifications	
Table 3. D.C. Electrical Characteristics	
Table 4. Gyroscope Noise and Current Consumption	
Table 5. Accelerometer Noise and Current Consumption	
Table 6. A.C. Electrical Characteristics	
Table 7. Other Electrical Specifications	13
Table 8. I ² C Timing Characteristics	
Table 9. SPI Timing Characteristics (8MHz Operation)	15
Table 10. Absolute Maximum Ratings	
Table 12. Bill of Materials	19
Table 13. Power Modes for ICM-20608-G	23
Table 14. Table of Interrupt Sources	24
Table 15. Serial Interface	25
Table 16. I ² C Terms	27



1. GENERAL DESCRIPTION

1.2 PURPOSE AND SCOPE

This document is a product specification, providing a description, specifications, and design related information on the ICM-20608- G^{TM} MotionTracking device. The device is housed in a small 3x3x0.75mm 16-pin LGA package.

1.3 PRODUCT OVERVIEW

The ICM-20608-G is a 6-axis MotionTracking device that combines a 3-axis gyroscope, and a 3-axis accelerometer in a small 3x3x0.75mm (16-pin LGA) package. It also features a 512-byte FIFO that can lower the traffic on the serial bus interface, and reduce power consumption by allowing the system processor to burst read sensor data and then go into a low-power mode. ICM-20608-G, with its 6-axis integration, enables manufacturers to eliminate the costly and complex selection, qualification, and system level integration of discrete devices, guaranteeing optimal motion performance for consumers.

The gyroscope has a programmable full-scale range of ± 250 , ± 500 , ± 1000 , and ± 2000 degrees/sec. The accelerometer has a user-programmable accelerometer full-scale range of $\pm 2g$, $\pm 4g$, $\pm 8g$, and $\pm 16g$. Factory-calibrated initial sensitivity of both sensors reduces production-line calibration requirements.

Other industry-leading features include on-chip 16-bit ADCs, programmable digital filters, an embedded temperature sensor, and programmable interrupts. The device features I²C and SPI serial interfaces, a VDD operating range of 1.71 to 3.45V, and a separate digital IO supply, VDDIO from 1.71V to 3.45V. Communication with all registers of the device is performed using either I²C at 400kHz or SPI at 8MHz.

By leveraging its patented and volume-proven CMOS-MEMS fabrication platform, which integrates MEMS wafers with companion CMOS electronics through wafer-level bonding, InvenSense has driven the package size down to a footprint and thickness of 3x3x0.75mm (16-pin LGA), to provide a very small yet high performance low cost package. The device provides high robustness by supporting 10,000q shock reliability.

1.4 APPLICATIONS

- Mobile phones and tablets
- Handset and portable gaming
- Motion-based game controllers
- 3D remote controls for Internet connected DTVs and set top boxes, 3D mice
- Wearable sensors for health, fitness and sports



2. FEATURES

2.1 GYROSCOPE FEATURES

The triple-axis MEMS gyroscope in the ICM-20608-G includes a wide range of features:

- Digital-output X-, Y-, and Z-axis angular rate sensors (gyroscopes) with a user-programmable full-scale range of ±250, ±500, ±1000, and ±2000°/sec and integrated 16-bit ADCs
- Digitally-programmable low-pass filter
- Factory calibrated sensitivity scale factor
- Self-test

2.2 ACCELEROMETER FEATURES

The triple-axis MEMS accelerometer in ICM-20608-G includes a wide range of features:

- Digital-output X-, Y-, and Z-axis accelerometer with a programmable full scale range of ±2g, ±4g, ±8g and ±16g and integrated 16-bit ADCs
- User-programmable interrupts
- Wake-on-motion interrupt for low power operation of applications processor
- Self-test

2.3 ADDITIONAL FEATURES

The ICM-20608-G includes the following additional features:

- Smallest and thinnest LGA package for portable devices: 3x3x0.75mm (16-pin LGA)
- Minimal cross-axis sensitivity between the accelerometer and gyroscope axes
- 512 byte FIFO buffer enables the applications processor to read the data in bursts
- Digital-output temperature sensor
- User-programmable digital filters for gyroscope, accelerometer, and temp sensor
- 10,000 q shock tolerant
- 400kHz Fast Mode I²C for communicating with all registers
- 8MHz SPI serial interface for communicating with all registers
- MEMS structure hermetically sealed and bonded at wafer level
- RoHS and Green compliant



3. ELECTRICAL CHARACTERISTICS

3.1 GYROSCOPE SPECIFICATIONS

Typical Operating Circuit of section 0, VDD = 1.8 V, VDDIO = 1.8 V, T_A = 25°C, unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES
	GYROSCOPE SENSITIVIT	Υ				
Full-Scale Range	FS_SEL=0		±250		°/s	3
	FS_SEL=1		±500		°/s	3
	FS_SEL=2		±1000		°/s	3
	FS_SEL=3		±2000		°/s	3
Gyroscope ADC Word Length			16		bits	3
Sensitivity Scale Factor	FS_SEL=0		131		LSB/(°/s)	3
	FS_SEL=1		65.5		LSB/(°/s)	3
	FS_SEL=2		32.8		LSB/(°/s)	3
	FS_SEL=3		16.4		LSB/(°/s)	3
Sensitivity Scale Factor Tolerance	25°C		±2		%	2
Sensitivity Scale Factor Variation Over Temperature	-40°C to +85°C		±3		%	1
Nonlinearity	Best fit straight line; 25°C		±0.1		%	1
Cross-Axis Sensitivity			±2		%	1
	ZERO-RATE OUTPUT (ZR	0)				
Initial ZRO Tolerance	25°C		±5		°/s	2
ZRO Variation Over Temperature	-40°C to +85°C		±0.1		°/s/°C	1
G	YROSCOPE NOISE PERFORMANC	E (FS_SEL=0	0)			
Noise Spectral Density			0.008		°/s/√Hz	1
Gyroscope Mechanical Frequencies		25	27	29	KHz	2
Low Pass Filter Response	Programmable Range	5		250	Hz	3
Gyroscope Start-Up Time	From Sleep mode		35		ms	1
Output Data Rate	Standard (duty-cycled) mode	3.91		500	Hz	1
	Low-Noise (active) mode	4		8000	Hz	1

Table 1. Gyroscope Specifications

Notes:

- 1. Derived from validation or characterization of parts, not guaranteed in production.
- 2. Tested in production.
- 3. Guaranteed by design.



3.2 ACCELEROMETER SPECIFICATIONS

Typical Operating Circuit of section 0, VDD = 1.8V, VDDIO = 1.8V, T_A =25°C, unless otherwise noted.

PARAMETER	COND	CONDITIONS			MAX	UNITS	NOTES			
ACCELEROMETER SENSITIVITY										
	AFS_SEL=0	AFS_SEL=0				g	3			
	AFS_SEL=1			±4		g	3			
Full-Scale Range	AFS_SEL=2			±8		g	3			
	AFS_SEL=3			±16		g	3			
ADC Word Length	Output in two's comple	ement format		16		bits	3			
	AFS_SEL=0	<u> </u>				LSB/g	3			
	AFS_SEL=1			8,192		LSB/g	3			
Sensitivity Scale Factor	AFS_SEL=2			4,096		LSB/g	3			
	AFS_SEL=3			2,048		LSB/g	3			
Initial Tolerance	Component-level			±2		%	2			
Sensitivity Change vs. Temperature	-40°C to +85°C AFS_SE Component-level	L=0		±0.016		%/°C	1			
Nonlinearity	Best Fit Straight Line			±0.5		%	1			
Cross-Axis Sensitivity				±2		%	1			
	:	ZERO-G OUTPUT								
Initial Tolerance	Component-level, all a	xes		±60		mg	1			
7 Classician Tanana	-40°C to +85°C,	X and Y axes		±0.5		m <i>g</i> /°C	1			
Zero-G Level Change vs. Temperature	Board-level	Z axis		±1		m <i>g</i> /°C	1			
	NO	ISE PERFORMANC	E							
Noise Spectral Density				250		μg/√Hz	1			
Low Pass Filter Response	Programmable Range	Programmable Range			218	Hz	3			
Intelligence Function Increment		5		4		mg/LSB	3			
Accelerometer Startup Time	From Sleep mode			20		ms	1			
Acceleronieter Startup Time	From Cold Start, 1ms V	_{DD} ramp		30		ms	1			
Output Data Rate		Standard (duty-cycled) mode			500	Hz	1			
	Low-Noise (active) mo	Low-Noise (active) mode			4000	Hz				

Table 2. Accelerometer Specifications

Notes:

- 1. Derived from validation or characterization of parts, not guaranteed in production.
- 2. Tested in production.
- 3. Guaranteed by design.



3.3 ELECTRICAL SPECIFICATIONS

3.3.1 D.C. Electrical Characteristics

Typical Operating Circuit of section 0, VDD = 1.8 V, VDDIO = 1.8 V, T_A=25°C, unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES			
	SUPPLY VOLTAGES								
VDD		1.71	1.8	3.45	V	1			
VDDIO		1.71	1.8	3.45	V	1			
	SUPPLY CURRENTS								
Low-Noise Mode	6-axis Gyroscope + Accelerometer		3		mA	1			
	3-axis Gyroscope		2.6		mA	1			
	3-axis Accelerometer, 4kHz ODR		390		μΑ	1			
Accelerometer Standard Mode	100Hz ODR, 1x averaging		57		μΑ	1			
Gyroscope Standard Mode	100Hz ODR, 1x averaging		1.6		mA	1			
Gyroscope Standard Mode	10Hz ODR, 1x averaging		1.3		mA	1			
6-Axis Standard Mode (Gyroscope Standard Mode; Accelerometer Low- Noise Mode)	100Hz ODR, 1x averaging		1.9		mA	1			
Full-Chip Sleep Mode			6		μΑ	1			
	TEMPERATURE RANGE								
Specified Temperature Range	Performance parameters are not applicable beyond Specified Temperature Range	-40		+85	°C	1			

Table 3. D.C. Electrical Characteristics

Notes:

1. Derived from validation or characterization of parts, not guaranteed in production.



3.3.2 Standard (Duty-Cycle) Mode Noise and Power Performance:

The following tables contain Gyroscope and Accelerometer noise and current consumption values for standard (duty-cycle) mode, for various ODRs and averaging filter settings. Please refer to the ICM-20608-G Register Map for further information about the registers referenced in the tables below.

FCHOICE	_B	0	0	0	0	0	0	0	0
G_AVGCFG		0	1	2	3	4	5	6	7
Average	es .	1x	2x	4x	8x	16x	32x	64x	128x
Ton (ms	5)	1.73	2.23	3.23	5.23	9.23	17.23	33.23	65.23
Noise BW	(Hz)	650.8	407.1	224.2	117.4	60.2	30.6	15.6	8.0
Noise (dps) TYP 0.008º/s/		0.20	0.16	0.12	0.09	0.06	0.04	0.03	0.02
SMPLRT_DIV	ODR (Hz)			Curre	ent Consum	ption (mA) 1	(mA) TYP		
255	3.9	1.3	1.3	1.3	1.3	1.4	1.4	1.5	1.8
99	10.0	1.3	1.3	1.4	1.4	1.5	1.6	1.9	2.5
64	15.4	1.4	1.4	1.4	1.5	1.6	1.8	2.2	N/A
32	30.3	1.4	1.4	1.5	1.6	1.8	2.2	N,	/ ^
19	50.0	1.5	1.5	1.6	1.8	2.1	2.8	IN/	A
9	100.0	1.6	1.7	1.9	2.2	3.0		N/A	
7	125.0	1.7	1.8	2.0	2.5	N/A			
4	200.0	1.9	2.1	2.5		NI/A			
3	250.0	2.1	2.3	2.7		N/A			
2	333.3	2.3	2.6		N/A				
1 500.0 2.9						N/A			

Table 4. Gyroscope Noise and Current Consumption

ACCEL_FCHC	ICE_B	1	0	0	0	0
A_DLPF_C	FG	Х	7	7	7	7
DEC2_CF	-G	Х	0	1	2	3
Average	es .	1x	4x	8x	16x	32x
Ton (ms	5)	1.084	1.84	2.84	4.84	8.84
Noise BW	(Hz)	1100.0	441.6	235.4	121.3	61.5
Noise (mg) TYP 250μg/√		8.3	5.3	3.8	2.8	2.0
SMPLRT_DIV	ODR (Hz)		Current C	onsumption	(μA) TYP	
255	3.9	8.4	9.4	10.8	13.6	19.2
127	7.8	9.8	11.9	14.7	20.3	31.4
63	15.6	12.8	17.0	22.5	33.7	55.9
31	31.3	18.7	27.1	38.2	60.4	104.9
15	62.5	30.4	47.2	69.4	113.9	202.8
7	125.0	57.4	87.5	132.0	220.9	N/A
3	250.0	100.9 168.1 257.0 N/A				
1	500.0	194.9	329.3		N/A	

Table 5. Accelerometer Noise and Current Consumption



3.3.3 A.C. Electrical Characteristics

Typical Operating Circuit of section 0, VDD = 1.8V, VDDIO = 1.8V, T_A =25°C, unless otherwise noted.

PARAMETERS	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES
	SUPPLIES					
Supply Ramp Time (T _{RAMP})	Monotonic ramp. Ramp rate is 10% to 90% of the final value	0.01		100	ms	1
	TEMPERATURE SEN	ISOR				
Operating Range	Ambient	-40		85	°C	1
Room Temperature Offset	25°C		0		°C	1
Sensitivity	Untrimmed		326.8		LSB/°C	1
	POWER-ON RESE	т				
Supply Ramp Time (T _{RAMP})	Valid power-on RESET	0.01		100	ms	1
Ctart up time for register read/unite	From power-up		11	100	ms	1
Start-up time for register read/write	From sleep			5	ms	1
I ² C ADDRESS	AD0 = 0 AD0 = 1		1101000 1101001			
	DIGITAL INPUTS (FSYNC, ADO	, SCLK, SDI, CS)				
V _{IH} , High Level Input Voltage		0.7*VDDIO			V	
V _{IL} , Low Level Input Voltage				0.3*VDD IO	V	1
C _I , Input Capacitance			< 10		pF	
	DIGITAL OUTPUT (SD	O, INT)				
V _{он} , High Level Output Voltage	R _{LOAD} =1MΩ;	0.9*VDDIO			V	
V _{OL1} , Low-Level Output Voltage	R_{LOAD} =1 $M\Omega$;			0.1*VDD IO	V	
V _{OLINT} , INT Low-Level Output Voltage	OPEN=1, 0.3mA sink Current			0.1	V	1
Output Leakage Current	OPEN=1		100		nA	
t _{INT} , INT Pulse Width	LATCH_INT_EN=0		50		μs	
	12C 1/O (SCL, SDA	4)				
V _{IL} , Low-Level Input Voltage		-0.5V		0.3*VDD IO	V	
V _{IH} , High-Level Input Voltage		0.7*VDDIO		VDDIO + 0.5V	V	
V _{hys} , Hysteresis			0.1*VDD IO		V	1
V _{OL} , Low-Level Output Voltage	3mA sink current	0		0.4	V	1 •
I _{ဝレ} Low-Level Output Current	V _{OL} =0.4V V _{OL} =0.6V		3 6		mA mA	
Output Leakage Current			100		nA	
t _{of} , Output Fall Time from V _{IHmax} to V _{ILmax}	C _b bus capacitance in pf	20+0.1C _b		300	ns	



		INTERNAL CLOCK SOURCE	E			
Sample Rate	FCHOICE_B=1,2,3 SMPLRT_DIV=0		32		kHz	2
	FCHOICE_B=0; DLPFCFG=0 or 7 SMPLRT_DIV=0		8		kHz	2
	FCHOICE_B=0; DLPFCFG=1,2,3,4,5,6; SMPLRT_DIV=0		1		kHz	2
Clock Frequency	CLK_SEL=0, 6 or gyro inactive; 25°C	-5		+5	%	1
Initial Tolerance	CLK_SEL=1,2,3,4,5 and gyro active; 25°C	-1		+1	%	1
Frequency Variation over Temperature	CLK_SEL=0,6 or gyro inactive	-10		+10	%	1
	CLK_SEL=1,2,3,4,5 and gyro active	-1		+1	%	1

Table 6. A.C. Electrical Characteristics

Notes:

- 1. Derived from validation or characterization of parts, not guaranteed in production.
- 2. Guaranteed by design.



3.3.4 Other Electrical Specifications

Typical Operating Circuit of section 0, VDD = 1.8V, VDDIO = 1.8V, T_A =25°C, unless otherwise noted.

PARAMETERS	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES
	SERIAL IN	ITERFACE				
SPI Operating Frequency, All Registers	Low-Speed Characterization		100 ±10%		kHz	1
Read/Write	High-Speed Characterization		1	8	MHz	1, 2
SPI Modes			Modes 0 and 3			
J ² C On careting Factoring	All registers, Fast-mode			400	kHz	1
I ² C Operating Frequency	All registers, Standard-mode			100	kHz	1

Table 7. Other Electrical Specifications

Notes:

- 1. Derived from validation or characterization of parts, not guaranteed in production.
- 2. SPI clock duty cycle between 45% and 55% should be used for 8-MHz operation.



3.4 I2C TIMING CHARACTERIZATION

Typical Operating Circuit of section 0, VDD = 1.8V, VDDIO = 1.8V, T_A =25°C, unless otherwise noted.

PARAMETERS	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES
I ² C TIMING	I ² C FAST-MODE					
f _{SCL} , SCL Clock Frequency				400	kHz	1
t _{HD.STA} , (Repeated) START Condition Hold Time		0.6			μs	1
t _{LOW} , SCL Low Period		1.3			μs	1
t _{HIGH} , SCL High Period		0.6			μs	1
t _{SU.STA} , Repeated START Condition Setup Time		0.6			μs	1
t _{HD.DAT} , SDA Data Hold Time		0			μs	1
t _{SU.DAT} , SDA Data Setup Time		100			ns	1
t _r , SDA and SCL Rise Time	C _b bus cap. from 10 to 400pF	20+0.1C _b		300	ns	1
t _f , SDA and SCL Fall Time	C _b bus cap. from 10 to 400pF	20+0.1C _b		300	ns	1
t _{SU.STO} , STOP Condition Setup Time		0.6			μs	1
t _{BUF} , Bus Free Time Between STOP and START Condition		1.3			μs	1
C _b , Capacitive Load for each Bus Line			< 400		pF	1
t _{VD.DAT} , Data Valid Time				0.9	μs	1
t _{VD.ACK} , Data Valid Acknowledge Time				0.9	μs	1

Table 8. I²C Timing Characteristics

Notes:

1. Based on characterization of 5 parts over temperature and voltage as mounted on evaluation board or in sockets




Figure 1. I2C Bus Timing Diagram



3.5 SPI TIMING CHARACTERIZATION

Typical Operating Circuit of section 0, VDD = 1.8V, VDDIO = 1.8V, T_A=25°C, unless otherwise noted.

PARAMETERS	CONDITIONS	MIN	ТҮР	MAX	UNITS	NOTES
SPI TIMING						
f _{SCLK} , SCLK Clock Frequency				8	MHz	1
t _{LOW} , SCLK Low Period		56			ns	1
t _{HIGH} , SCLK High Period		56			ns	1
t _{SU.CS} , CS Setup Time		2			ns	1
t _{HD.CS} , CS Hold Time		63			ns	1
t _{SU.SDI} , SDI Setup Time		3			ns	1
t _{HD.SDI} , SDI Hold Time		7			ns	1
t _{VD.SDO} , SDO Valid Time	C _{load} = 20pF			40	ns	1
t _{DIS.SDO} , SDO Output Disable Time				20	ns	1
t _{Fall} , SCLK Fall Time				6.5	ns	2
t _{Rise} , SCLK Rise Time				6.5	ns	2
t _{DIS.SDO} , SDO Output Disable Time				20	ns	1

Table 9. SPI Timing Characteristics (8MHz Operation)

Notes:

- 1. Based on characterization of 5 parts over temperature and voltage as mounted on evaluation board or in sockets
- 2. Based on calculation from other parameter values




Figure 2. SPI Bus Timing Diagram



3.6 ABSOLUTE MAXIMUM RATINGS

Stress above those listed as "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these conditions is not implied. Exposure to the absolute maximum ratings conditions for extended periods may affect device reliability.

PARAMETER	RATING
Supply Voltage, VDD	-0.5V to +4V
Supply Voltage, VDDIO	-0.5V to +4V
REGOUT	-0.5V to 2V
Input Voltage Level (AD0, FSYNC, SCL, SDA)	-0.5V to VDD + 0.5V
Acceleration (Any Axis, unpowered)	10,000g for 0.2ms
Operating Temperature Range	-40°C to +85°C
Storage Temperature Range	-40°C to +125°C
Electrostatic Discharge (ESD) Protection	2kV (HBM); 250V (MM)
Latch-up	JEDEC Class II (2),125°C ±100mA

Table 10. Absolute Maximum Ratings




4. APPLICATIONS INFORMATION

4.1 PIN OUT DIAGRAM AND SIGNAL DESCRIPTION

PIN NUMBER	PIN NAME	PIN DESCRIPTION
1	VDDIO	Digital I/O supply voltage
2	SCL/SCLK	I ² C serial clock (SCL); SPI serial clock (SCLK)
3	SDA/SDI	I ² C serial data (SDA); SPI serial data input (SDI)
4	AD0/SDO	I ² C slave address LSB (AD0); SPI serial data output (SDO)
5	CS	Chip select (0 = SPI mode; $1 = I^2C$ mode)
6	INT	Interrupt digital output (totem pole or open-drain)
7	RESV	Reserved. Do not connect.
8	FSYNC	Synchronization digital input (optional). Connect to GND if unused.
9	RESV	Reserved. Connect to GND.
10	RESV	Reserved. Connect to GND.
11	RESV	Reserved. Connect to GND.
12	RESV	Reserved. Connect to GND.
13	GND	Connect to GND
14	REGOUT	Regulator filter capacitor connection
15	RESV	Reserved. Connect to GND.
16	VDD	Power Supply

Table 11. Signal Descriptions



+Z

LGA Package (Top View) 16-pin, 3mm x 3mm x 0.75mm Typical Footprint and thickness

Orientation of Axes of Sensitivity and Polarity of Rotation

Figure 3. Pin out Diagram for ICM-20608-G 3.0x3.0x0.75mm LGA



4.2 TYPICAL OPERATING CIRCUIT




Figure 4. ICM-20608-G I2C Operation Application Schematic




Figure 5. ICM-20608-G SPI Operation Application Schematic



4.3. BILL OF MATERIALS FOR EXTERNAL COMPONENTS

COMPONENT	LABEL	SPECIFICATION	QUANTITY
REGOUT Capacitor	C1	Ceramic, X7R, 0.47μF ±10%, 2V	1
VDD Bunger Campaitans	C2	Ceramic, X7R, 0.1μF ±10%, 4V	1
VDD Bypass Capacitors	C4	Ceramic, X7R, 2.2μF ±10%, 4V	1
VDDIO Bypass Capacitor	C3	Ceramic, X7R, 10nF ±10%, 4V	1

Table 11. Bill of Materials

4.4. BLOCK DIAGRAM




Figure 6. ICM-20608-G Block Diagram



4.5. OVERVIEW

The ICM-20608-G is comprised of the following key blocks and functions:

- Three-axis MEMS rate gyroscope sensor with 16-bit ADCs and signal conditioning
- Three-axis MEMS accelerometer sensor with 16-bit ADCs and signal conditioning
- Primary I²C and SPI serial communications interfaces
- Self-Test
- Clocking
- Sensor Data Registers
- FIFO
- Interrupts
- Digital-Output Temperature Sensor
- Bias and LDOs
- Charge Pump
- Standard Power Modes

4.6. THREE-AXIS MEMS GYROSCOPE WITH 16-BIT ADCS AND SIGNAL CONDITIONING

The ICM-20608-G consists of three independent vibratory MEMS rate gyroscopes, which detect rotation about the X-, Y-, and Z-Axes. When the gyros are rotated about any of the sense axes, the Coriolis Effect causes a vibration that is detected by a capacitive pickoff. The resulting signal is amplified, demodulated, and filtered to produce a voltage that is proportional to the angular rate. This voltage is digitized using individual on-chip 16-bit Analog-to-Digital Converters (ADCs) to sample each axis. The full-scale range of the gyro sensors may be digitally programmed to ±250, ±500, ±1000, or ±2000 degrees per second (dps). The ADC sample rate is programmable from 8,000 samples per second, down to 3.9 samples per second, and user-selectable low-pass filters enable a wide range of cut-off frequencies.

4.7. THREE-AXIS MEMS ACCELEROMETER WITH 16-BIT ADCS AND SIGNAL CONDITIONING

The ICM-20608-G's 3-Axis accelerometer uses separate proof masses for each axis. Acceleration along a particular axis induces displacement on the corresponding proof mass, and capacitive sensors detect the displacement differentially. The ICM-20608-G's architecture reduces the accelerometers' susceptibility to fabrication variations as well as to thermal drift. When the device is placed on a flat surface, it will measure 0g on the X- and Y-axes and +1g on the Z-axis. The accelerometers' scale factor is calibrated at the factory and is nominally independent of supply voltage. Each sensor has a dedicated sigma-delta ADC for providing digital outputs. The full scale range of the digital output can be adjusted to $\pm 2g$, $\pm 4g$, $\pm 8g$, or $\pm 16g$.

4.8. I2C AND SPI SERIAL COMMUNICATIONS INTERFACES

The ICM-20608-G communicates to a system processor using either a SPI or an I^2C serial interface. The ICM-20608-G always acts as a slave when communicating to the system processor. The LSB of the I^2C slave address is set by pin 4 (AD0).

4.8.1 ICM-20608-G Solution Using I2C Interface

In the figure below, the system processor is an I²C master to the ICM-20608-G.






Figure 7. ICM-20608-G Solution Using I²C Interface

4.8.2 ICM-20608-G Solution Using SPI Interface

In the figure below, the system processor is an SPI master to the ICM-20608-G. Pins 2, 3, 4, and 5 are used to support the SCLK, SDI, SDO, and CS signals for SPI communications.




Figure 8. ICM-20608-G Solution Using SPI Interface



4.9 SELF-TEST

Self-test allows for the testing of the mechanical and electrical portions of the sensors. The self-test for each measurement axis can be activated by means of the gyroscope and accelerometer self-test registers (registers 27 and 28).

When the self-test is activated, the electronics cause the sensors to be actuated and produce an output signal. The output signal is used to observe the self-test response.

The self-test response is defined as follows:

Self-test response = Sensor output with self-test enabled - Sensor output with self-test disabled

The self-test response for each gyroscope axis is defined in the gyroscope specification table, while that for each accelerometer axis is defined in the accelerometer specification table.

When the value of the self-test response is within the specified min/max limits of the product specification, the part has passed self-test. When the self-test response exceeds the min/max values, the part is deemed to have failed self-test. It is recommended to use InvenSense MotionApps software for executing self-test.

4.10 CLOCKING

The ICM-20608-G has a flexible clocking scheme, allowing a variety of internal clock sources to be used for the internal synchronous circuitry. This synchronous circuitry includes the signal conditioning and ADCs, and various control circuits and registers. An on-chip PLL provides flexibility in the allowable inputs for generating this clock.

Allowable internal sources for generating the internal clock are:

- a) An internal relaxation oscillator
- b) Auto-select between internal relaxation oscillator and gyroscope MEMS oscillator to use the best available source

The only setting supporting specified performance in all modes is option b). It is recommended that option b) be used.

4.11 SENSOR DATA REGISTERS

The sensor data registers contain the latest gyroscope, accelerometer, and temperature measurement data. They are read-only registers, and are accessed via the serial interface. Data from these registers may be read anytime.

4.12 FIFO

The ICM-20608-G contains a 512-byte FIFO register that is accessible via the Serial Interface. The FIFO configuration register determines which data is written into the FIFO. Possible choices include gyro data, accelerometer data, temperature readings, and FSYNC input. A FIFO counter keeps track of how many bytes of valid data are contained in the FIFO. The FIFO register supports burst reads. The interrupt function may be used to determine when new data is available.

The ICM-20608-G allows FIFO read in standard (duty cycle) accelerometer mode.

4.13 INTERRUPTS

Interrupt functionality is configured via the Interrupt Configuration register. Items that are configurable include the INT pin configuration, the interrupt latching and clearing method, and triggers for the interrupt. Items that can trigger an interrupt are (1) Clock generator locked to new reference oscillator (used when switching clock sources); (2) new data is available to be read (from the FIFO and Data registers); (3) accelerometer event interrupts; (4) FIFO overflow. The interrupt status can be read from the Interrupt Status register.

4.14 DIGITAL-OUTPUT TEMPERATURE SENSOR

An on-chip temperature sensor and ADC are used to measure the ICM-20608-G die temperature. The readings from the ADC can be read from the FIFO or the Sensor Data registers.



4.15 BIAS AND LDOS

The bias and LDO section generates the internal supply and the reference voltages and currents required by the ICM-20608-G. Its two inputs are an unregulated VDD and a VDDIO logic reference supply voltage. The LDO output is bypassed by a capacitor at REGOUT. For further details on the capacitor, please refer to the Bill of Materials for External Components.

4.16 CHARGE PUMP

An on-chip charge pump generates the high voltage required for the MEMS oscillator.

4.17 POWER MODES

The following table lists the user-accessible power modes for ICM-20608-G.

MODE	NAME	GYRO	ACCEL		
1	Sleep Mode	Off	Off		
2	Standby Mode	Drive On	Off		
3	Accelerometer Standard Mode	Off	Duty-Cycled		
4	Accelerometer Low-Noise Mode	er Low-Noise Mode Off			
5	Gyroscope Standard Mode	Duty-Cycled	Off		
6	Gyroscope Low-Noise Mode	On	Off		
7	6-Axis Low-Noise Mode	On	On		
8	6-Axis Standard Mode	Duty-Cycled	On		

Table 12. Power Modes for ICM-20608-G



5 PROGRAMMABLE INTERRUPTS

The ICM-20608-G has a programmable interrupt system which can generate an interrupt signal on the INT pin. Status flags indicate the source of an interrupt. Interrupt sources may be enabled and disabled individually.

INTERRUPT NAME	MODULE
Motion Detection	Motion
FIFO Overflow	FIFO
Data Ready	Sensor Registers

Table 13. Table of Interrupt Sources

5.1 WAKE-ON-MOTION INTERRUPT

The ICM-20608-G provides motion detection capability. A qualifying motion sample is one where the high passed sample from any axis has an absolute value exceeding a user-programmable threshold. The following steps explain how to configure the Wake-on-Motion Interrupt.

Step 1: Ensure that Accelerometer is running

- In PWR_MGMT_1 register (0x6B) set CYCLE = 0, SLEEP = 0, and GYRO_STANDBY = 0
- In PWR_MGMT_2 register (0x6C) set STBY_XA = STBY_YA = STBY_ZA = 0, and STBY_XG = STBY_YG = STBY_ZG = 1

Step 2: Accelerometer Configuration

In ACCEL_CONFIG2 register (0x1D) set ACCEL_FCHOICE_B = 0 and A_DLPF_CFG[2:0] = 1 (b001)

Step 3: Enable Motion Interrupt

In INT_ENABLE register (0x38) set WOM_INT_EN = 111 to enable motion interrupt

Step 4: Set Motion Threshold

Set the motion threshold in ACCEL_WOM_THR register (0x1F)

Step 5: Enable Accelerometer Hardware Intelligence

In ACCEL_INTEL_CTRL register (0x69) set ACCEL_INTEL_EN = ACCEL_INTEL_MODE = 1; Ensure that bit 0 is set to 0.

Step 6: Set Frequency of Wake-Up

• In Standard Mode Configuration register (0x1E) set LPOSC_CLKSEL[3:0] for a sample rate as indicated in the register map

Step 7: Enable Cycle Mode (Accelerometer Standard Mode)

In PWR_MGMT_1 register (0x6B) set CYCLE = 1



6 DIGITAL INTERFACE

6.1 I2C AND SPI SERIAL INTERFACES

The internal registers and memory of the ICM-20608-G can be accessed using either I²C at 400 kHz or SPI at 8MHz. SPI operates in four-wire mode.

PIN NUMBER	PIN NAME	PIN DESCRIPTION
1	VDDIO	Digital I/O supply voltage.
4	AD0 / SDO	I ² C Slave Address LSB (AD0); SPI serial data output (SDO)
2	SCL / SCLK	I ² C serial clock (SCL); SPI serial clock (SCLK)
3	SDA / SDI	I ² C serial data (SDA); SPI serial data input (SDI)

Table 14. Serial Interface

Note:

To prevent switching into I²C mode when using SPI, the I²C interface should be disabled by setting the *I2C_IF_DIS* configuration bit. Setting this bit should be performed immediately after waiting for the time specified by the "Start-Up Time for Register Read/Write" in Section 3.3.3.

6.2 I2C INTERFACE

 I^2C is a two-wire interface comprised of the signals serial data (SDA) and serial clock (SCL). In general, the lines are open-drain and bidirectional. In a generalized I^2C interface implementation, attached devices can be a master or a slave. The master device puts the slave address on the bus, and the slave device with the matching address acknowledges the master.

The ICM-20608-G always operates as a slave device when communicating to the system processor, which thus acts as the master. SDA and SCL lines typically need pull-up resistors to VDD. The maximum bus speed is 400 kHz.

The slave address of the ICM-20608-G is b110100X which is 7 bits long. The LSB bit of the 7 bit address is determined by the logic level on pin AD0. This allows two ICM-20608-Gs to be connected to the same I²C bus. When used in this configuration, the address of one of the devices should be b1101000 (pin AD0 is logic low) and the address of the other should be b1101001 (pin AD0 is logic high).

6.3 I2C COMMUNICATIONS PROTOCOL

START (S) and STOP (P) Conditions

Communication on the I²C bus starts when the master puts the START condition (S) on the bus, which is defined as a HIGH-to-LOW transition of the SDA line while SCL line is HIGH (see figure below). The bus is considered to be busy until the master puts a STOP condition (P) on the bus, which is defined as a LOW to HIGH transition on the SDA line while SCL is HIGH (see figure below). Additionally, the bus remains busy if a repeated START (Sr) is generated instead of a STOP condition.




Figure 9. START and STOP Conditions



Data Format / Acknowledge

I²C data bytes are defined to be 8-bits long. There is no restriction to the number of bytes transmitted per data transfer. Each byte transferred must be followed by an acknowledge (ACK) signal. The clock for the acknowledge signal is generated by the master, while the receiver generates the actual acknowledge signal by pulling down SDA and holding it low during the HIGH portion of the acknowledge clock pulse.

If a slave is busy and cannot transmit or receive another byte of data until some other task has been performed, it can hold SCL LOW, thus forcing the master into a wait state. Normal data transfer resumes when the slave is ready, and releases the clock line (refer to the following figure).




Figure 10. Acknowledge on the I²C Bus

Communications

After beginning communications with the START condition (S), the master sends a 7-bit slave address followed by an 8th bit, the read/write bit. The read/write bit indicates whether the master is receiving data from or is writing to the slave device. Then, the master releases the SDA line and waits for the acknowledge signal (ACK) from the slave device. Each byte transferred must be followed by an acknowledge bit. To acknowledge, the slave device pulls the SDA line LOW and keeps it LOW for the high period of the SCL line. Data transmission is always terminated by the master with a STOP condition (P), thus freeing the communications line. However, the master can generate a repeated START condition (Sr), and address another slave without first generating a STOP condition (P). A LOW to HIGH transition on the SDA line while SCL is HIGH defines the stop condition. All SDA changes should take place when SCL is low, with the exception of start and stop conditions.




Figure 11. Complete I²C Data Transfer



To write the internal ICM-20608-G registers, the master transmits the start condition (S), followed by the I²C address and the write bit (0). At the 9th clock cycle (when the clock is high), the ICM-20608-G acknowledges the transfer. Then the master puts the register address (RA) on the bus. After the ICM-20608-G acknowledges the reception of the register address, the master puts the register data onto the bus. This is followed by the ACK signal, and data transfer may be concluded by the stop condition (P). To write multiple bytes after the last ACK signal, the master can continue outputting data rather than transmitting a stop signal. In this case, the ICM-20608-G automatically increments the register address and loads the data to the appropriate register. The following figures show single and two-byte write sequences.

Single-Byte Write Sequence

Master	S	AD+W		RA		DATA		Р
Slave			ACK		ACK		ACK	

Burst Write Sequence

Master	S	AD+W		RA		DATA		DATA		Р
Slave			ACK		ACK		ACK		ACK	

To read the internal ICM-20608-G registers, the master sends a start condition, followed by the I^2C address and a write bit, and then the register address that is going to be read. Upon receiving the ACK signal from the ICM-20608-G, the master transmits a start signal followed by the slave address and read bit. As a result, the ICM-20608-G sends an ACK signal and the data. The communication ends with a not acknowledge (NACK) signal and a stop bit from master. The NACK condition is defined such that the SDA line remains high at the 9^{th} clock cycle. The following figures show single and two-byte read sequences.

Single-Byte Read Sequence

Master	S	AD+W		RA		S	AD+R			NACK	Р
Slave			ACK		ACK			ACK	DATA		

Burst Read Sequence

Ī	Master	S	AD+W		RA		S	AD+R			ACK		NACK	Р
Ī	Slave			ACK		ACK			ACK	DATA		DATA		

6.4 I²C TERMS

SIGNAL	DESCRIPTION
S	Start Condition: SDA goes from high to low while SCL is high
AD	Slave I ² C address
W	Write bit (0)
R	Read bit (1)
ACK	Acknowledge: SDA line is low while the SCL line is high at the 9 th clock cycle
NACK	Not-Acknowledge: SDA line stays high at the 9 th clock cycle
RA	ICM-20608-G internal register address
DATA	Transmit or received data
Р	Stop condition: SDA going from low to high while SCL is high

Table 15. I²C Terms



6.5 SPI INTERFACE

SPI is a 4-wire synchronous serial interface that uses two control lines and two data lines. The ICM-20608-G always operates as a Slave device during standard Master-Slave SPI operation.

With respect to the Master, the Serial Clock output (SCLK), the Serial Data Output (SDO) and the Serial Data Input (SDI) are shared among the Slave devices. Each SPI slave device requires its own Chip Select (CS) line from the master.

CS goes low (active) at the start of transmission and goes back high (inactive) at the end. Only one CS line is active at a time, ensuring that only one slave is selected at any given time. The CS lines of the non-selected slave devices are held high, causing their SDO lines to remain in a high-impedance (high-z) state so that they do not interfere with any active devices.

SPI Operational Features

- 1. Data is delivered MSB first and LSB last
- 2. Data is latched on the rising edge of SCLK
- 3. Data should be transitioned on the falling edge of SCLK
- 4. The maximum frequency of SCLK is 8MHz
- 5. SPI read and write operations are completed in 16 or more clock cycles (two or more bytes). The first byte contains the SPI Address, and the following byte(s) contain(s) the SPI data. The first bit of the first byte contains the Read/Write bit and indicates the Read (1) or Write (0) operation. The following 7 bits contain the Register Address. In cases of multiple-byte Read/Writes, data is two or more bytes:

SPI Address format

MSB							LSB
R/W	A6	A5	A4	А3	A2	A1	Α0

SPI Data format

MSB							LSB
D7	D6	D5	D4	D3	D2	D1	D0

6. Supports Single or Burst Read/Writes.




Figure 12. Typical SPI Master/Slave Configuration



7 ASSEMBLY

This section provides general guidelines for assembling InvenSense Micro Electro-Mechanical Systems (MEMS) gyros packaged in LGA package.

ORIENTATION OF AXES

The diagram below shows the orientation of the axes of sensitivity and the polarity of rotation. Note the pin 1 identifier (•) in the figure.





Figure 13. Orientation of Axes of Sensitivity and Polarity of Rotation



PACKAGE DIMENSIONS

16 Lead LGA (3x3x0.75) mm NiAu pad finish





		DIMENSIONS IN MILLIMETERS			
	SYMBOLS	MIN	NOM	MAX	
Total Thickness	Α	0.7	0.75	0.8	
Substrate Thickness	A1		0.105	REF	
Mold Thickness	A2		0.63	REF	
Body Size —	D	2.9	3	3.1	
Body Size	E	2.9	3	3.1	
Lead Width	W	0.2	0.25	0.3	
Lead Length	L	0.3	0.35	0.4	
Lead Pitch	е		0.5	BSC	
Lead Count	n		16		
Edge Ball Center to Center	D1		2	BSC	
Euge Bail Center to Center	E1		1	BSC	
Rady Contou to Contoot Rall	SD			BSC	
Body Center to Contact Ball	SE			BSC	
Ball Width	b				
Ball Diameter					
Ball Opening					
Ball Pitch	e1				
Ball Count	n1				
Pre-Solder					
Package Edge Tolerance	aaa		0.1		
Mold Flatness	bbb	0.2			
Coplanarity	ddd	0.08			
Ball Offset (Package)	eee				
Ball Offset (Ball)	fff				
Lead Edge to Package Edge	М	0.01	0.06	0.11	



8 PART NUMBER PACKAGE MARKING

The part number package marking for ICM-20608-G devices is summarized below:

PART NUMBER	PART NUMBER PACKAGE MARKING		
ICM-20608-G	IC268G		



9.REFERENCE

Please refer to "InvenSense MEMS Handling Application Note (AN-IVS-0002A-00)" for the following information:

- Manufacturing Recommendations
 - o Assembly Guidelines and Recommendations
 - PCB Design Guidelines and Recommendations
 - o MEMS Handling Instructions
 - o ESD Considerations
 - o Reflow Specification
 - Storage Specifications
 - Package Marking Specification
 - o Tape & Reel Specification
 - o Reel & Pizza Box Label
 - o Packaging
 - o Representative Shipping Carton Label
- Compliance
 - o Environmental Compliance
 - o DRC Compliance
 - o Compliance Declaration Disclaimer



REVISION HISTORY

REVISION DATE	REVISION NUMBER	DESCRIPTION	
06/15/2015	1.0	Initial Release	



COMPLIANCE DECLARATION DISCLAIMER

InvenSense believes the environmental and other compliance information given in this document to be correct but cannot guarantee accuracy or completeness. Conformity documents substantiating the specifications and component characteristics are on file. InvenSense subcontracts manufacturing and the information contained herein is based on data received from vendors and suppliers, which has not been validated by InvenSense.

This information furnished by InvenSense is believed to be accurate and reliable. However, no responsibility is assumed by InvenSense for its use, or for any infringements of patents or other rights of third parties that may result from its use. Specifications are subject to change without notice. InvenSense reserves the right to make changes to this product, including its circuits and software, in order to improve its design and/or performance, without prior notice. InvenSense makes no warranties, neither expressed nor implied, regarding the information and specifications contained in this document. InvenSense assumes no responsibility for any claims or damages arising from information contained in this document, or from the use of products and services detailed therein. This includes, but is not limited to, claims or damages based on the infringement of patents, copyrights, mask work and/or other intellectual property rights.

Certain intellectual property owned by InvenSense and described in this document is patent protected. No license is granted by implication or otherwise under any patent or patent rights of InvenSense. This publication supersedes and replaces all information previously supplied. Trademarks that are registered trademarks are the property of their respective companies. InvenSense sensors should not be used or sold in the development, storage, production or utilization of any conventional or mass-destructive weapons or for any other weapons or life threatening applications, as well as in any other life critical applications such as medical equipment, transportation, aerospace and nuclear instruments, undersea equipment, power plant equipment, disaster prevention and crime prevention equipment.

©2015 InvenSense, Inc. All rights reserved. InvenSense, MotionTracking, MotionProcessing, MotionProcessor, MotionFusion, MotionApps, DMP, AAR, and the InvenSense logo are trademarks of InvenSense, Inc. Other company and product names may be trademarks of the respective companies with which they are associated.



©2015 InvenSense, Inc. All rights reserved.